




MATRIKX[®] + CR1

Extruded Activated Carbon Block Filter

Chlorine Taste and Odor and Cyst Reduction

- *0.5 µm Nominal Filtration*
- *Cyst Reduction Based on NSF/ANSI Standard 53*
- *Turbidity Reduction Based on NSF/ANSI Standard 53*
- *Outstanding Chlorine Taste and Odor Reduction*
- *Performance Tested and Verified by Independent Laboratory Testing*



MATRIKX[®] + CR1 is the most effective filter available for the combined reduction of cysts and control of large volumes and concentrations of chlorine taste and odor. Manufactured using a patented, solid-state extrusion process, the MATRIKX[®] + CR1 meets NSF/ANSI Standard 53, Turbidity and Cyst Reduction, including *Cryptosporidium*, *Giardia*, *Entamoeba* and *Toxoplasma*.

Made of "Genuine MATRIKX[®] Extruded Carbon," the MATRIKX[®] + CR1 is a rigid, carbon block composite designed to deliver chlorine taste and odor reduction at >99% @ 2.5 GPM for 10,000 gallons.

The MATRIKX[®] + CR1 is ideal for use in food service applications.

Technical Specifications and Order Information

Part No.	O.D. x Length	Weight	Chlorine Taste & Odor Reduction Capacity @ Flow	Nominal µm Rating	Initial ΔP @ Flow
19-250-125-975	2.50" x 9.75"	0.85 lbs.	>10,000 gal. @ 2.5 GPM	0.5 µm	8.0 psid @ 1.0 GPM
19-250-125-20	2.50" x 20"	1.95 lbs.	>20,000 gal. @ 5.0 GPM	0.5 µm	8.0 psid @ 2.0 GPM



ORDER INFORMATION

Special order filters are available in varying sizes with lengths from 1" to 60".

Standard filters are finished with a prefiltration medium. A protective polypropylene netting is applied to the exterior of the cartridge. Polypropylene end caps with compression gaskets fit most standard housings.

Inquire concerning alternative filter finishing options, including alternative end cap and housing interface styles, a wide range of non-standard extruded filter sizes, and non-standard prefiltration systems.

EXTRUDED CARBON = EXCEPTIONAL VALUE

MATRIKX® + CR1 filters consist of activated carbon particles fused into a uniform block with enhanced adsorptive capacity and efficiency. MATRIKX® + CR1 filters flow in a radial (outside-to-inside) direction, providing increased dirt capacity and low pressure drop. Unlike granular activated carbon (GAC) filters, MATRIKX® + CR1 cartridges will not channel or bypass due to the extreme uniformity of their extruded activated carbon core. Service life of the MATRIKX® + CR1 filter is greatly extended by a layer of prefiltration medium.

- No channeling
- No fluidizing
- No bypassing
- Eliminates release of carbon fines
- Lowest extractables, pure materials of construction
- Maximum service life and resistance to fouling
- Graded density filtration design
- Manufactured using FDA-compliant materials

Made in the USA.

Distributed by:



LIMITED LIABILITY

KX Industries, L.P. makes no warranties of any kind, expressed or implied, statutory or otherwise, and expressly disclaims all warranties of every kind, concerning the product, including, without limitation, warranties of merchantability and fitness for a particular purpose, except that this product should be capable of performing as described in this product's data sheet. KX Industries, L.P.'s obligation shall be limited solely to the refund of the purchase price or replacement of the product proven defective, in KX Industries, L.P.'s sole discretion. Determination of suitability of this product for uses and applications contemplated by Buyer shall be the sole responsibility of Buyer. Use of this product constitutes Buyer's acceptance of this Limited Liability.

269 South Lambert Road
Orange, CT 06477-3502
Telephone: 203-799-9000
Fax: 203-799-7000
Toll Free: 800-462-8745
E-mail sales@kxindustries.com
www.kxindustries.com



NOTES

1. Performance of a given MATRIKX® extruded carbon filter varies in direct proportion to the total weight of carbon in each filter. For example, a 4.25" O.D. x 20" L MATRIKX® filter contains approximately seven times as much activated carbon as a 2.50" O.D. x 9.75" L MATRIKX® filter, and will therefore have seven times the rated chlorine taste and odor capacity when operated at seven times the rated flow of the smaller cartridge. Hence, rated flow is based on maintaining identical contact/residence times for all filters.
2. Projected chlorine taste and odor reduction capacity when tested in accordance with NSF/ANSI Standard 42 protocol.
3. Nominal particulate rating (0.5 µm) is for >85% of a given size as determined from single-pass particle counting results.*
4. Absolute particulate rating (1 µm) is for >99.9% of particles of a given size as determined from single-pass particle counting results.**

* Nominal Filter Rating: Filter rating indicating the approximate size particle, the majority of which will not pass through the filter. It is generally interpreted as meaning that 85% of the particles of the size equal to the nominal micron rating will be retained by the filter. (WQA Glossary of Terms, Third Edition, 3-97).

** Absolute Filter Rating: Filter rating meaning that 99.9% (or essentially all) of the particles larger than a specific micron rating will be trapped on or within the filter. (WQA Glossary of Terms, Third Edition, 3-97).

WARNINGS:

Maximum Operating Temperature:	125°F
Maximum Operating Pressure:	250 psig
Maximum Differential Pressure:	100 psid
Collapse Pressure:	200 psid

MATRIKX® filters are not to be autoclaved or steam-sterilized.

Use this MATRIKX® + CR1 carbon filter only with microbiologically safe and adequately disinfected water, as it is not designed to kill or remove bacteria or viruses.

Actual results obtained will vary with various combinations of organic contaminants, changes in pH or other conditions encountered in actual use.

All information presented here is based on data believed to be reliable. It is offered for evaluation and verification, but is not to be considered a warranty of any kind.

MATRIKX® filters are designed to fit most standard household and commercial or industrial housings.

Contact KX Industries, L.P. to check filter housing compatibility.

This cartridge must be placed in an appropriate housing and flushed for a minimum of 5 minutes prior to use.

This Product is made or covered by one or more of the following United States Patents: 5,019,311; 5,147,722; 5,189,092; 5,249,948; 5,331,037; 5,922,803; 5,946,342; 6,061,384 and applicable foreign equivalents.

© 2005 KX Industries, L.P. All rights reserved. KX, the KX Logo, MATRIKX and the "GENUINE MATRIKX EXTRUDED CARBON" seal are registered trademarks of KX Industries, L.P.